


# Hookup Wire

UL Style: 1571/10064/1061  
 UL Voltage Rating: 30V/30V/300V  
 UL Temp: 80°C/105°C/80°C



PVC, Irradiated Cross-Linked PVC, and ETFE insulations available.

Various colors and gauges available upon request.

UL approved.

Suitable for JST connectors.

**APPLICATIONS** Internal wiring of electronic equipment.

Eco-Index: RoHS Values

<1000ppm <100ppm <1000ppm <1000ppm <1000ppm

Pb

Cd

Cr+6

Hg

PBDE's  
PPB's

**PHYSICAL CONSTRUCTION DESCRIPTION** Insulated hook-up wire, consisting of 1 conductor, unshielded, and unjacketed.



| Part No.        | Conductor | Insulation | UL Style | Conductor Resistance<br>Ω/Mft. @20°C | Insulation Resistance<br>MΩ/KFT @20°C | JST Connector |
|-----------------|-----------|------------|----------|--------------------------------------|---------------------------------------|---------------|
| 40565-1-S-10000 | 28 7/36   | XL PVC     | 1571     | 68                                   | 3                                     | ZR            |
| 40564-1-S-8000  | 30 7/38   | XL PVC     | 1571     | 108                                  | 3                                     | SR            |
| 40566-1-S-16000 | 32 7/40   | XL PVC     | 1571     | 182                                  | 3                                     | SSR           |
| 40462-1-S-4000  | 32 7/40   | ETFE       | 10064    | 224                                  | 305                                   | SUR           |
| 40085-1-10000   | 28 7/36   | PVC        | 1061     | 68                                   | 4000                                  | DS/KR         |

Notes: Some products in stock in white; consult factory for details.  
 All data is for reference only and is subject to change.