


Product Highlights

- RoHS compliant
- OM2, OM3, & OM4 cables utilize Corning ClearCurve glass.
- 250 micron loose tube design allows for higher fiber strand counts in a smaller overall diameter cable
- Ideal for MT and MTP/MPO style connectors
- No gel design makes installation quick, easy and clean
- Each fiber is color coded for easy identification
- Flexible and easy to handle
- Lightweight, flexible Aramid yarns enhance strength

Options

- Standard colors are yellow for singlemode, orange for multimode and aqua for 10 Gigabit -other colors are available
- OM4 cables with extended 10 gigabit distances are available



Zip Cord

Diagram scale approx. 5:1

NanoCore™ Loose Tube No Gel Distribution Zip Cord (Plenum)

(UL) OFNP c(UL) FT6

Fiber Count	50 UM OM2	50 UM OM3	50 UM OM4	8.3 UM OS2	8.3 UM OS2BI
12	61546-12	61539-12	61882-12	61547-12	61713-12
24	61546-24	61539-24	61882-24	61547-24	61713-24

Optical Specifications

TIA/EIA-568-C.3 | ISO/IEC 11801, 2nd edition | Telcordia GR-409-CORE

HCM Fiber Performance Parameters	Max Attenuation (dB/Km)		Min Bandwidth OFL MHz-Km		Min Bandwidth* MHz-Km		Gigabit Ethernet Support Distance (meters)		10 Gigabit Ethernet Support Distance (meters)	
	850 nm	1300 nm	850 nm	1300 nm	850 nm	1300 nm	850 nm	1300 nm	850 nm	1300 nm
OM1	3.5	1.0	200	500	220	na	300	550	33	na
OM2	3.5	1.0	700	500	850	na	750	550	150	na
OM3	3.25	1.0	1500	500	2000	na	1000	550	300	na
OM4	3.25	1.0	3500	500	4700	na	1100	550	550	na

*EMBc for OM2, OM3 & OM4 fibers. RML for OM1 fibers.

	1310 nm	1550 nm
OS2	0.50	0.5
OS2 BI**	0.50	0.5

**OS2 BI utilizes bend-insensitive optical glass

HCM reserves the right to revise any specifications.

Loose Tube

Indoor

NanoCore™ Loose Tube No Gel Distribution Zip Cord (Plenum)

(UL) OFNP c(UL) FT6

FIBER COUNT	CABLE O.D.		MAXIMUM LOAD INSTALL		OPERATION		CABLE WEIGHT	
	in.	mm	lbs-f	N	lbs-f	N	lbs/1000 ft	kg/1000m
12	.118 x .255	3.0 x 6.47	128	569	64	284	11.3	16.8
24	.118 x .255	3.0 x 6.47	128	569	64	284	11.4	17.0

Mechanical Specifications

- Bend radius, no load = 10x cable overall diameter
- Bend radius, load = 15x cable overall diameter




10 Gigabit Applications

IEEE standard	Wavelength	Transmission	Fiber type	Length (m)
10GBASE-SR	850nm	Serialized	OM1	33
			OM2	82
			OM3	300
			OM4	550
10GBASE-LR	1310nm	Serialized	SM	10,000 - 25,000
10GBASE-LRM	1310nm	Serialized	OM1	220
			OM3	260
10GBASE-ER	1550nm	Serialized	SM	40,000
10GBASE-LX4	1300nm	WDM	MM	240-300
			SM	10,000

For complete application list, refer to page 91.

Features



DIELECTRIC MATERIALS	PLENUM
Overall Jacket	Low-smoke, flame-retardant thermoplastic

