




HCM StratusFlex: Highly Bend-Tolerant Fiber Assemblies**Routing for singlemode fiber isn't a problem anymore!****Features:**

- Superior Optical Power Sustainability by 6 holes
- Small Bending Radius applicable
 - 5mm bending radius
- Compatible with Standard SMF
 - 0.2dB typical connector loss with SMF
- High Reliability
 - lower than 10^{-5} failure probability with 5mm bend for 20 years

**Bend Characteristics:****Applications:**



Small Cabinet



Fiber Tying



Corner Routing



**Available in terminated jumper and coil cord designs.
Call for product information & availability**