


Optical Active HDMI® Cable Good to

100

**Full Resolution to 1080p deep color,
3D and 4K2K available
in Plenum cable style.**

**Standards-Based – Proven at HDMI® Global Compliance Centers.
No Extra Power Needed* – All Power Supplied from HDMI® Port.
Available in UL Listed Plenum design.
Trusted Hitachi Cabling Technology – ultra-small O/E conversion.**

No extra power supply* No converter box Available now.



*No extra power supply is needed, in case a HDMI® sink consumes 15mA or less.

Parameter	Target Specification
Length	Standard Lengths: 20m, 30m, 40m, 50 meters. Up to 100 meters available.
Connector	Compatible with HDMI® standard
HDMI® Level	HDMI® High speed, No Ethernet
Performance	High Speed HDMI® (3.4 Gb/s x 3 channels + clock) (480p, 720p, 1080i and 1080p deep color, 4K, 3D. HEC is not supported.)
Cable Diameter	UL Plenum approved cable 5.5mm nominal
Operating Temperature	0-50 degrees C
Storage Temperature	-20 to 70 degrees C
Storage Humidity	5-85% RH, non-condensing
Cable Types Available	OFNP (Plenum)
Compliance	<ul style="list-style-type: none"> •RoHS •UL 910 •Class 1M laser product; •ESD: Jedec HBM/MM, IEC 61000-4-2
Tensile Strength	150 N (installation)
Minimum Cable Bend Radius	A) Cable Near Connectors 100 mm B) Central Section of Cable 100 mm

Hitachi Cable, Ltd.

Akihabara UDX,
4-14-1, Sotokanda, Chiyodaku, Tokyo 101-8971, JAPAN
Phone: +81-3-5256-5454
FAX: +81-3-5256-3240

Hitachi Cable Manchester

900 Holt Avenue
Manchester, NH 03109 USA
Phone: 603-669-4347 Fax: 603-669-9621
www.hcm.hitachi.com